

254mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock #15-182 3-5 DAYS

⊖ 1 ⊕ **A\$1,956.80**

ADD TO CART

Qty 1-4
A\$1,956.80
Qty 5+
A\$1,761.60
Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm):
1064

Focal Length FL (mm):
254.00

Maximum Diameter (mm):
122

Scan Angle (°):
±25.00

Scan Field (mm): 157.0 x 157.0
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 304.6
Wavelength Range (nm): 1064
Range Distance (mm): 360.6
Focus Size Diameter, 1/e² (μm): 25
Input Beam Diameter, 1/e² (mm): 20
Maximum Length (mm): 76.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View