

[« See all 227 Products in Family](#)
[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Cylinder Lenses](#) / [Illumination Grade Cylinder Lenses](#) / [Illumination Grade PCX Cylinder Lenses](#)
**TECHSPEC®**

# 25.4mm H x 25.4mm L x 200mm FL Uncoated, Illumination Grade PCX Cylinder Lens


 Stock #35-027 **20+ In Stock**

 - 1 + **A\$124<sup>.00</sup>**
[ADD TO CART](#)

Volume Pricing	
Qty 1-5	A\$124.00 each
Qty 6-25	A\$112.00 each
Qty 26-49	A\$106.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	Zemax:zar
Zemax:zmx	eDrawing:eprt
Code V:seq	EO Spec Sheet
<a href="#">Download All</a>	

## General

**Type:** Cylinder Lens, Plano-Convex

## Physical & Mechanical Properties

<b>Center Thickness CT (mm):</b>	2.10	<b>Center Thickness Tolerance (mm):</b>	±0.1
<b>Dimensional Tolerance (mm):</b>	+0.0/-0.2	<b>Dimensions (mm):</b>	25.4 x 25.4
<b>Edge Thickness ET (mm):</b>	1.31		

## Optical Properties

<b>Effective Focal Length EFL (mm):</b>	200.00	<b>Substrate:</b> <b>N-BK7</b>	
<b>f/#:</b>	7.8740157480315	<b>Numerical Aperture NA:</b>	0.06
<b>Coating:</b>	Uncoated	<b>Wavelength Range (nm):</b>	350 - 2200
<b>Back Focal Length BFL (mm):</b>	198.38	<b>Focal Length Tolerance (%):</b>	±3
<b>Radius R<sub>1</sub> (mm):</b>	103.36	<b>Surface Quality:</b>	60-40

## Regulatory Compliance

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- N-BK7 Substrate for Broadband Performance
- Cost-Effective for OEM Integration
- Multiple Coating Options Available

TECHSPEC® Illumination Grade PCX Cylinder Lenses are similar to Plano-Convex (PCX) lenses in profile, but include a portion of a cylinder instead of a sphere. These lenses focus light in one dimension and can transform a point of light into a line. TECHSPEC® Illumination Grade PCX Cylinder Lenses are available in circular and rectangular versions, along with multiple coating options. Cylinder lenses are ideal for line projection in machine vision applications or guidance systems.

**Note:** For negative focal length cylinder lenses, see our [TECHSPEC® Illumination Grade PCV Cylinder Lenses](#).




## Technical Information

## Related Products



Illumination Grade PCV  
Cylinder Lenses



Imaging Grade PCX  
Cylinder Lenses



Laser Grade Laser Line  
Cylinder Lenses



Laser Grade Broadband  
Cylinder Lenses

## Frequently Purchased Together



#35-023 - 12.7mm H x 12.7mm L x 150mm FL Uncoated, Illumination Grade PCX Cylinder Lens  
**A\$110.00**

Qty

#35-028 - 25.4mm H x 25.4mm L x 250mm FL Uncoated, Illumination Grade PCX Cylinder Lens  
**A\$124.00**

Qty

#49-848 - 25.4mm Dia. x 38.1mm FL, Uncoated, Plano-Convex Lens  
**A\$56.00**

Qty

#49-849 - 25.4mm Dia. x 50.8mm FL, Uncoated, Plano-Convex Lens  
**A\$52.40**

Qty

# Resources

## Media Type

- Application Note
- Trending in Optics
- Published Article
- FAQ
- Glossary
- Video

APPLICATION NOTE

Anti-Reflection (AR) Coatings

APPLICATION NOTE

Laser Beam Shaping Overview

TRENDING IN OPTICS

Non-Circular Optics for System Miniaturization

APPLICATION NOTE

What are Cylinder Lenses?

APPLICATION NOTE

Considerations When Using Cylinder Lenses

PUBLISHED ARTICLE

Cylinder Lenses for Beam Shaping

[View More](#)