

25.4mm Length, M4 and M6, Steel Post



Stock #72-761 NEW 1 In Stock

⊖ 1 ⊕ A\$9²⁰

ADD TO CART

Volume Pricing

| | |
|--------|--------------|
| Qty 1+ | A\$9.20 each |
|--------|--------------|

| | |
|------------|-------------------------------|
| Need More? | Request Quote |
|------------|-------------------------------|

Product Downloads

General

Metric Type:

Physical & Mechanical Properties

25.40 ±0.1 Length (mm):

1 Length (inches):

12.70 -0.02/-0.05 Diameter (mm):

Diameter (inches):

Threading & Mounting

Male Thread:
Thread 1: M4 x0.7
Thread 2: M6 x1

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Product Details

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x0.7/M6 x1.0 for Metric; 8-32/¼-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

Note: All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.