

2.5mm CA, VIS Coated, 70 Diopter Focus Range, Corning® Varioptic® Variable Focus Liquid Lens Development Kit



2.5mm CA, VIS Coated, 70 Diopter Focus Range, Corning® Varioptic® Variable Focus Liquid Lens Development Kit



Stock **#19-357** CLEARANCE 3-5 DAYS

- 1 + **A\$963.12**

ADD TO CART

Qty 1+
A\$963.12

Volume Pricing
[Request Quote](#)

Get Product Downloads



Diameter (mm):
9.40 (packaged lens, 7.75 bare lens)

Coating:
VIS

Type: Development Kit
Clear Aperture CA (mm): 2.5
Contents of Kit: Coming® Varioptic® A-25H0-D0 Lens (without cable) A-25H0-D0-P07 Lens (with straight flex cable : 4 pins) Maxim MAX14574 Driver Board (with 4 pin connector and 6 pin connector for thermistor populated 6 pin FPC) USB-MFlexiboard (with 4 and 6 pin connector and USB compatibility) M4 thread holder for lens Bent Flex Cable FPC-A-03 Control Software Documentation Package
Focus Range: -35 to +35 diopter
Model Number: D-A-25H0-D0
Operating Temperature (°C): -20 to +60
Storage Temperature (°C): -40 to +85
Thickness (mm): 3.50 (packaged lens, 2.15 bare lens)
Transmission (%): 96 @ 587nm
Transmitted Wavefront Error, RMS: 70nm
Typical Applications: Very close auto-focus or continuous auto-focus applications in portable devices and in laser or lighting applications for variable focus and expansion control. Features 3X higher dynamic range over the A-25HX lens.

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View