

TECHSPEC®

25.4mm Square x -50 FL, 532nm AR Coated, Laser Grade PCV Cylinder Lens


 Stock #37-601 **1 In Stock**

- 1 +

A\$445^{.00}
ADD TO CART

Volume Pricing	
Qty 1-5	A\$445.00 each
Qty 6-25	A\$401.00 each
Qty 26-49	A\$381.00 each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
Curve (xlsx):xlsx	Zemax:zar
Zemax:zmx	eDrawing:eam
Code V:seq	EO Spec Sheet
Download All	

General

Type: Cylinder Lens, Plano-Concave

Physical & Mechanical Properties

Bevel:	Protective as needed	Center Thickness CT (mm):	3.00
Center Thickness Tolerance (mm):	±0.1	Clear Aperture CA (mm):	22.86 x 22.86
Dimensional Tolerance (mm):	+0.0/-0.025	Dimensions (mm):	25.4 x 25.4
Edge Thickness ET (mm):	6.64	Axial Twist (arcmin):	<3

Optical Properties

Effective Focal Length EFL (mm):	-50.00	Substrate: Fused Silica (Corning 7980)	
f/#:	2	Numerical Aperture NA:	0.25
Coating:	Laser V-Coat (532nm)	Back Focal Length BFL (mm):	-52.06
Coating Specification:	R _{abs} <0.25% @ 532nm	Design Wavelength DWL (nm):	532
Focal Length Specification	587.6	Radius R₁ (mm):	22.93

Wavelength (nm):		Damage Threshold, By Design: ⓘ	10 J/cm ² @ 532nm, 20ns, 20Hz
Surface Quality:	20-10	Irregularity (P-V) @ 632.8nm:	λ/4
Power (P-V) @ 632.8nm:	1.5λ	Power Axis Wedge (arcmin):	<4.5
Plano Axis Wedge (arcmin):	<3		

Regulatory Compliance

RoHS 2015:	Compliant	Reach 209:	Compliant
Certificate of Conformance:	View		

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- <0.25% AR Coated for Nd:YAG Harmonics
- <3 Arcminute Wedge Tolerance
- Fused Silica Substrate

TECHSPEC® Laser Grade Laser Line Cylinder Lenses are manufactured with tightly controlled geometric wedge tolerances to facilitate drop in compatibility. These laser line cylinder lenses feature laser grade optical specifications including 20–10 surface quality and λ/4 surface irregularity on both plano and cylindrical surfaces. TECHSPEC Laser Grade Laser Line Cylinder Lenses are available in 266nm, 355nm, 532nm, and 1064nm AR coated versions, with specified laser induced damage thresholds. These fused silica lenses are ideal for demanding laser machining and medical applications.

Related Products




Metric Rectangular Optic Mounts



Laser Grade Broadband Cylinder Lenses




Laser Beam Shaping



Cylinder Lenses

Frequently Purchased Together



#43-927 - 2" x 2" Sq., Plastic Optical Window
A\$48.80

Qty



#47-335 - 12.0mm Dia. x 42.0mm FL, VIS 0° Coated, Plano-Convex Lens
A\$76.00

Qty



#47-357 - 25.0mm Dia. x 750.0mm FL, VIS 0° Coated, Plano-Convex Lens
A\$76.00

Qty



#48-413 - 50mm Square Uncoated, B270 Window
A\$107.20

Qty

Resources

Media Type

- Application Note
- Trending in Optics
- Published Article
- FAQ
- Glossary
- Video

APPLICATION NOTE

Anti-Reflection (AR) Coatings

APPLICATION NOTE

Laser Beam Shaping Overview

TRENDING IN OPTICS

Non-Circular Optics for System Miniaturization

APPLICATION NOTE

What are Cylinder Lenses?

APPLICATION NOTE

Considerations When Using Cylinder Lenses

PUBLISHED ARTICLE

Cylinder Lenses for Beam Shaping

[View More](#)