

TECHSPEC® 25mm Dia. x 20mm FL, VIS Coated, Hybrid Asphere



TECHSPEC® Plastic Hybrid Aspheric Lenses

Stock **#66-001** CLEARANCE 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$158.40

ADD TO CART

Qty 1-24

A\$158.40

Qty 25+

A\$126.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
20.00 @ 587.6nm

Numerical Aperture NA:
0.63

Back Focal Length BFL (mm): 13.89
Substrate:  Zeonex E48R
Aspheric Design Wavelength (nm): 587.6
Coating: BBAR (425-675nm)
Coating Specification: R _{avg} ≤0.75% @425 - 675nm
Surface Quality: 60-40
Clear Aperture CA (mm): 23.00
Edge Thickness ET (mm): 3.4
Center Thickness CT (mm): 10.00 ±0.10
f/#: 0.8
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to +70
Radius R₂ (mm): 120
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 425 - 675
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View