

TECHSPEC®

25mm Dia., 0.40 Numerical Aperture, 900-1700nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-999-INK** 10-15 DAYS

[Other Coating Options](#)

- 1 + **A\$584.00**

ADD TO CART

Qty 1-5
A\$584.00
Qty 6+
A\$467.20
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):
31.25 @ 587.6nm

Numerical Aperture NA: 0.40
Back Focal Length BFL (mm): 23.67
Substrate: ☐ N-BK7
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: SWIR+ (900-1700nm)
Coating Specification: R _{avg} <0.5% @ 900 - 1700nm @ ±30° AOI R _{abs} <1.5% @ 900 - 1700nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 22.50
Edge Thickness ET (mm): 6.30
Center Thickness CT (mm): 11.50 ±0.10
f/#: 1.25
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 900 - 1700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
