

[See all 76 Products in Family](#)

TECHSPEC<sup>®</sup>

25mm, Aluminum & VIS 0° Coated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock **#48-552** 20+ In Stock

-

1

+

A\$174<sup>40</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | A\$174.40 each                |
| Qty 6-25       | A\$139.20 each                |
| Qty 26-49      | A\$131.20 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                             |
|----------------------------------|-----------------------------|
| Right Angle Prism                | Type:                       |
| Physical & Mechanical Properties |                             |
| ±0.1                             | Dimensional Tolerance (mm): |
| Protective as needed             | Bevel:                      |

|                                                                                                     |                                                       |
|-----------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| 35.40                                                                                               | Length of Hypotenuse (mm):                            |
| 25.00                                                                                               | Length of Legs (mm):                                  |
| Optical Properties                                                                                  |                                                       |
| VS 0° & Aluminized                                                                                  | Coating:                                              |
| N-BK7                                                                                               | Substrate: <input type="checkbox"/>                   |
| 60-40                                                                                               | Surface Quality:                                      |
| ±2                                                                                                  | Angle Tolerance (arcmin):                             |
| Left-Handed                                                                                         | Image Orientation:                                    |
| Hypotenuse: R <sub>avg</sub> >85% @ 400 - 700nm<br>Legs: R <sub>avg</sub> ≤0.4% @ 425 - 675nm       | Coating Specification:                                |
| 90                                                                                                  | Ray Deviation (°):                                    |
| 425 - 675                                                                                           | Wavelength Range (nm):                                |
| Hypotenuse: 0.3 J/cm <sup>2</sup> @ 532nm & 1064nm, 10ns<br>Legs: 5 J/cm <sup>2</sup> @ 532nm, 10ns | Damage Threshold, By Design: <input type="checkbox"/> |
| 1.25                                                                                                | Power (fringes) @ 632.8nm:                            |
| 0.50                                                                                                | Irregularity (fringes) @ 632.8nm:                     |
| Regulatory Compliance                                                                               |                                                       |
| Compliant                                                                                           | RoHS 2015:                                            |
| Compliant                                                                                           | Reach 219:                                            |
| View                                                                                                | Certificate of Conformance:                           |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Ray Deviation of 90°
- Left Handed Image
- Available with Aluminized and AR Coated Faces
- Additional [Right Angle Prism](#) Options Available

TECHSPEC® N-BK7 Right Angle Prisms are made from precision N-BK7 for use in a variety of visible light applications. Right angle prisms are generally used to bend image paths or redirect light at 90°. This produces a left-handed image, and depending on the orientation of the prism, the image may be inverted or reverted. TECHSPEC® N-BK7 Right Angle Prisms can also be used in combination for image/beam displacement. These right-angle prisms are additionally offered with aluminized and AR Coated surfaces.

## Technical Information



Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram

