

TECHSPEC® 25mm Dia 0.50 NA, 532nm V-Coat, Aspheric Lens



TECHSPEC® Laser Line Coated Aspheric Lenses

Stock **#33-015** 3-5 DAYS

[Other Coating Options](#)

- 1 + **A\$872.00**

ADD TO CART

Qty 1-5

A\$872.00

Qty 6+

A\$697.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 18.32
Substrate: ☐ Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 532
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Laser V-Coat (532nm)
Coating Specification: R _{abs} <0.25% @ 532nm
Centering (arcmin): ≤5
Surface Quality: 60–40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 1.75
Center Thickness CT (mm): 9.75 ±0.1
f/#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Conjugate Distance: Infinite
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 20ns, 20Hz
Power (diopters): 40.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant