

TECHSPEC[®] 25mm Dia 0.11 NA, *N*/40 Uncoated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#17-333** [CONTACT US](#)

-

1

+

A\$1,278^{.40}

ADD TO CART

Volume Pricing	
Qty 1-5	A\$1,278.40 each
Qty 6-10	A\$1,150.40 each
Qty 11-25	A\$1,073.60 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens

Type:

Physical & Mechanical Properties

25.00 +0/-0.025

Diameter (mm):

<1	Centering (arcmin):
22.5	Clear Aperture CA (mm):
3.85	Edge Thickness ET (mm):
5.50 ±0.1	Center Thickness CT (mm):
Protective as needed	Bevel:

Plano	Shape of Back Surface:
-------	------------------------

Optical Properties

100.00 @355nm	Effective Focal Length EFL (mm):
0.11	Numerical Aperture NA:

96.30	Back Focal Length BFL (mm):
-------	-----------------------------

Fused Silica (Corning 7980)	Substrate: ☐
-----------------------------	-------------------------------------

355	Aspheric Design Wavelength (nm):
-----	----------------------------------

λ/40	Asphere Figure Error, RMS @ 632.8nm:
------	--------------------------------------

Uncoated	Coating:
----------	----------

40-20	Surface Quality:
-------	------------------

4	f/#:
---	------

Infinite	Conjugate Distance:
----------	---------------------

10.00	Power (diopters):
-------	-------------------

Regulatory Compliance



View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Low Coefficient of Thermal Expansion
- Precision and High Precision Options
- High Numerical Apertures to Maximize Throughput

TECHSPEC® UV Fused Silica Aspheric Lenses offer the benefits of an aspheric element combined with the manufacturing precision of state-of-the-art grinding and polishing equipment. These fused silica optics can be easily designed and integrated into complex optical systems with the available prescription data. Featuring low f/#'s, which allow for a larger aperture and thus more light gathering and focusing performance, these fused silica lenses are computer-optimized to eliminate spherical and minimize higher order aberrations. TECHSPEC® UV Fused Silica Aspheric Lenses offer a low coefficient of thermal expansion, making them ideal for applications in metrology, beam-focusing or collimating, and OEM integration. These lenses are available in a variety of coating options and are offered in sizes ranging from 10-50mm.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts