

TECHSPEC®

25mm Dia., 0.25 Numerical Aperture, 600-1050nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-977-INK** 10-15 DAYS

[Other Coating Options](#)

- 1 + **A\$584.00**

ADD TO CART

Qty 1-5

A\$584.00

Qty 6+

A\$467.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):
50.00 @ 587.6nm

Numerical Aperture NA: 0.25
Back Focal Length BFL (mm): 45.23
Substrate: N-BK7
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: NIR+ (600-1050nm)
Coating Specification: R _{avg} <0.5% @ 600 - 1050nm @ ±30° AOI R _{abs} <1.5% @ 600 - 1050nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 24.00
Edge Thickness ET (mm): 4.14
Center Thickness CT (mm): 7.24 ±0.10
f#: 2.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View