


**TECHSPEC® 25mm Dia. 2° Beam Dev. Fused Silica Wedge Prism 532nm Laser V-Coat**



TECHSPEC Fused Silica Wedge Prisms

Stock #39-119 CLEARANCE **10 In Stock**

⊖ 1 ⊕ A\$177<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$177.60 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

**Note:**  
Specify this is S1 & S2 power and irregularity, not the overall power of the wedge

**Physical & Mechanical Properties**

Diameter (mm):

25.00

Thickness (mm):

3.00

Bevel:

Protective as needed

Wedge Angle (arcmin):  
4° 11'14"

## Optical Properties

Angle Tolerance (arcsec):  
15

Coating:  
Laser V-Coat (532nm)

Design Wavelength DWL (nm):  
532

Substrate:   
Fused Silica (Corning 7980)

Surface Quality:  
20-10

Image Orientation:  
Beam Deviation

Coating Specification:  
 $R_{\text{abs}} < 0.25\% @ 532\text{nm}$

Damage Threshold, By Design:   
10 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz

Power (fringes) @ 632.8nm:  
0.50

Irregularity (fringes) @ 632.8nm:  
0.20

Ray Deviation @ 355nm (°):  
2.00

Power (diopters):  
3.49

Wedge Angle (°):  
4.19°

## Material Properties

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):  
0.52

## Regulatory Compliance

RoHS 2015:  
Compliant

Reach 209:  
Compliant

Certificate of Conformance:  
[View](#)


## Product Details


- Deviates Laser Beam Path from 0.5° - 5.0°
- Ideal for UV to NIR Beam Steering Applications from 250 to 1064nm
- Ideal for High Power Beam Steering Applications

TECHSPEC® Fused Silica Wedge Prisms are designed for a range of laser beam steering applications requiring UV-VIS or first through fourth Nd:YAG harmonic Anti-Reflection Coatings. They are optimized to ensure the highest level of system performance using tightly controlled specifications including  $M10$  surface flatness, 20-10 surface quality, and a wedge tolerance of 15 or 30 arcseconds. The Nd:YAG coated versions feature high transmittance and guaranteed laser damage thresholds specific to the design wavelength. TECHSPEC® Fused Silica Wedge Prisms utilize a wedge design to deviate laser beam path from 0.5° – 5°. By creating a risley prism pair using two wedge prisms with the same ray deviation, custom beam steering up to two times the wedge deviation is possible. A low coefficient of thermal expansion ensures accurate beam steering in high power laser applications.

**Note:** Power Diopter is defined as 1cm deviation at a distance of 1m from the prism. TECHSPEC® Wedge Prisms are also available in [N-BK7 versions](#).

## Technical Information





## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).