

TECHSPEC®

25mm Dia., 0.83 Numerical Aperture, 600-1050nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-982-INK** 10-15 DAYS

[Other Coating Options](#)



1



A\$744.00

ADD TO CART

Qty 1-5

A\$744.00

Qty 6+

A\$595.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Numerical Aperture NA: 0.83
Back Focal Length BFL (mm): 9.24
Substrate: N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: NIR+ (600-1050nm)
Coating Specification: R _{avg} <0.5% @ 600 - 1050nm @ ±30° AOI R _{abs} <1.5% @ 600 - 1050nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 22.50
Edge Thickness ET (mm): 3.31
Center Thickness CT (mm): 10.40 ±0.10
f#: 0.60
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View