


**TECHSPEC® 25mm Dia. 2mm Thick VIS-EXT Coated, 1λ Fused Silica Window**

TECHSPEC® 1λ UV Fused Silica Windows

Stock #25-195 **9 In Stock**   **A\$192<sup>.00</sup>****ADD TO CART**

Volume Pricing	
Qty 1-5	<b>A\$192.00</b> each
Qty 6-25	<b>A\$152.80</b> each
Qty 26-49	<b>A\$143.20</b> each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

**SPECIFICATIONS****General****Type:**

Protective Window

**Physical & Mechanical Properties**

Bevel:	Protective as needed
Clear Aperture (%):	90
Clear Aperture CA (mm):	22.50
Diameter (mm):	25.00 +0.00/-0.20
Thickness (mm):	2.00 ±0.38
Edges:	Fine Ground
Knoop Hardness (kg/mm <sup>2</sup> ):	522.00
Parallelism (arcmin):	<5
Poisson's Ratio:	0.16
Young's Modulus (GPa):	73

## Optical Properties

Abbe Number (v <sub>d</sub> ):	67.8
Coating:	UV-EXT (350-700nm)
Coating Specification:	R <sub>avg</sub> ≤ 0.5% @ 350 - 700nm
Index of Refraction (n <sub>d</sub> ):	1.458
Substrate:	Fused Silica (Corning 7980)
Surface Quality:	60-40
Transmitted Wavefront, P-V:	1λ
Wavelength Range (nm):	350 - 700
Damage Threshold, Reference:	5 J/cm <sup>2</sup> @ 532nm, 10ns

## Material Properties

Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C):	0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm <sup>3</sup> ):	2.20

## Regulatory Compliance

RoHS 2015:	Compliant
Certificate of Conformance:	<a href="#">View</a>
Reach 235:	Compliant







## PRODUCT DETAILS


- Available Uncoated or with Broadband Anti-Reflection Coatings
- Ideal for Cost Sensitive Broadband Applications
- Circular and Square Sizes from 5mm to 100mm
- [N4](#) or [N10](#) UV Fused Silica Windows Also Available

TECHSPEC® 1λ UV Fused Silica Windows are precision manufactured using UV-grade synthetic fused silica. In addition to superior transmission, the synthetic fused silica of these optical windows exhibits higher thermal properties, exceptional purity, and excellent environmental durability for demanding applications. The windows are ideal for cost-sensitive broadband applications and are available uncoated or with broadband anti-reflection coatings. TECHSPEC® 1λ UV Fused Silica Windows have circular and square sizes ranging from 5mm to 100mm. [N4](#) or [N10](#) UV Fused Silica Windows are also available.


**Note:** New additions to this product family may be specified with a transmitted wavefront distortion (TWD) specification instead of a surface flatness. For more information on the difference between these two specifications, see our application note on [Understanding Optical Windows](#).

## TECHNICAL INFORMATION





## Fused Silica with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$\begin{aligned} R_{abs} &\leq 0.25\% @ 880\text{nm} \\ R_{avg} &\leq 1.25\% @ 400 - 870\text{nm} \\ R_{avg} &\leq 1.25\% @ 890 - 1000\text{nm} \end{aligned}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## Fused Silica with VIS 0° Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## Fused Silica with YAG-BBAR Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$\begin{aligned} R_{abs} &\leq 0.25\% @ 532\text{nm} \\ R_{abs} &\leq 0.25\% @ 1064\text{nm} \\ R_{avg} &\leq 1.0\% @ 500 - 1100\text{nm} \end{aligned}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## Fused Silica with NIR I Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## Fused Silica with NIR II Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 1.5\% @ 750 - 800\text{nm}$   
 $R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}$   
 $R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).