

TECHSPEC[®] 25mm Dia. 532nm 45°, Nd:YAG Laser Line Mirror



Nd:YAG ZERODUR Laser Line Mirrors

Stock **#26-427** **1 In Stock**

-

1

+

A\$368⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$368.00 each
Qty 6-25	A\$332.80 each
Need More?	Request Quote

Product Downloads

General	
Laser Mirror	Type:
Physical & Mechanical Properties	
25.00 +0.00/-0.20	Diameter (mm):
>90	Clear Aperture (%):
Parallelism (arcsec):	

30	
	Thickness (mm):
4.00 +/-0.2	
Optical Properties	
	Design Wavelength DWL (nm):
532	
	Wavelength Range (nm):
523 - 537	
	Substrate:
ZERODUR®	
	Angle of Incidence (°):
45	
	Reflection at DWL (%):
99.8	
	Coating:
Laser Mirror (532nm)	
	Coating Specification:
R _{abs} >99.8% @ 532nm @ 45° AOI R _{avg} >99.5% @ 523 - 537nm @ 45° AOI	
	Coating Type:
Dielectric	
	Surface Flatness (P-V):
λ/10	
	Surface Quality:
20-10	
	Damage Threshold, By Design:
15 J/cm² @ 532nm, 20ns, 20Hz	
Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
 - >99.5% Reflectivity at Nd:YAG Harmonic Frequencies
 - High Laser Damage Threshold Specifications
- Nd:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Nd:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of ±0.10 x 10-6/°C these mirrors are ideal for applications where the optics will be exposed to fluctuating temperatures. The Nd:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Nd:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with λ/10 flatness and 20-10 surface quality. These mirror are an excellent fit for laboratories and integration into larger powerful laser systems