

25mm Dia. Ge, IR Holographic Wire Grid Polarizer



25mm Dia. Ge, IR Holographic Wire Grid Polarizer, #62-776

Stock #62-776 3-5 DAYS

⊖ 1 ⊕ **A\$2,744.00**

ADD TO CART

Qty 1-5
A\$2,744.00
Qty 6+
A\$2,193.60
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
18.0

Diameter (mm):
25.00

Extinction Ratio: 300:1 @ 10.6μm
Substrate: □ Germanium (Ge)
Operating Temperature (°C): -20 to 75
Polarization: Notches on polarizer ring are aligned with wires of wire grid
Thickness (mm): 2.00
Transmission (%): >50
Type: Linear Polarizer
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Construction: Wire Grid
Groove Parallelism to Edge (°): N/A
Mount Thickness (mm): 5.0
Note: Notches on polarizer ring are aligned with wires of wire grid (max. reflection)
Ring Thickness (mm): ±0.1
Wavelength Range (nm): 8000 - 17000
Surface Flatness (P-V): λ/20 @ 10.6 μm
Damage Threshold, By Design: □ 50 W/cm²
Mount: Black Anodized Aluminum
Groove Density (grooves/mm): 2700.00
Mount Thickness Tolerance (mm): +0.2/-0.1

Regulatory Compliance

RoHS: Compliant
Reach 219: Compliant
Certificate of Conformance: View