


25mm Dia. High Contrast VIS-NIR Polarizer



Stock **#36-653** **12 In Stock**

A\$1,592⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$1,592.00 each
Qty 10+	A\$1,512.00 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

22.50 **Clear Aperture CA (mm):**

25.00 **Diameter (mm):**

2.00 ±0.2 **Thickness (mm):**

Dimensional Tolerance (mm):
+0.0/-0.2

Construction:
Nanoparticle

Clear Aperture (%):
90

Optical Properties

Angle of Incidence (°):
±20

Extinction Ratio:
>10,000:1 (650nm - 850nm)
>1,000:1 (650nm - 1000nm)

Substrate:
Soda Lime Float Glass

Surface Quality:
40-20

Transmission (%):
>84

Transmitted Wavefront, P-V:
< λ/4

Beam Deviation (arcmin):
<1

Polarization Axis Mark (%):
±2

Wavelength Range (nm):
600 - 1000

Environmental & Durability Factors

Operating Temperature (°C):
-20 to +120

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)


REACH 241:
[Compliant](#)



Product Details

- Multiple Wavelength Ranges for UV, VIS and NIR
- >100,000:1 Contrast Ratios Available
- Ideal for Use in Harsh Environments

UV, VIS-NIR, and NIR High Contrast Polarizers offer both versatility and performance over a wide range of wavelengths. These polarizers contain uniformly stretched silver nano-particles in a 220 ±25µm thick soda-lime glass laminated on a thicker soda-lime substrate for increased durability. UV, VIS-NIR, and NIR High Contrast Polarizers are ideal for harsh environments, can withstand up to 120°C, are resistant to UV-radiation and chemicals, and can be safely used in humid environments.

Technical Information





;