

TECHSPEC®

25mm Dia x 100mm FL VIS-NIR Coated, Illumination Grade PCX Cylinder Lens



Stock #69-781 3-5 DAYS

-

1

+

A\$140.80

ADD TO CART

Qty 1-5
A\$140.80
Qty 6+
A\$112.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
100.00

Substrate:
[N-BK7](#)

f/#:

4
Numerical Aperture NA: 0.13
Coating: VIS-NIR (400-1000nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): 97.98
Center Thickness CT (mm): 3.16
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.63
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 51.85
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant