

TECHSPEC[®] 25mm Dia x 20mm FL, Uncoated Molded Aspheric Condenser Lens



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#36-168** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

A\$51.20

ADD TO CART

Qty 1-10

A\$51.20

Qty 11+

A\$44.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
20.00 @ 587.6nm

Numerical Aperture NA:
0.625

Back Focal Length BFL (mm): 11.93
Substrate: Liba2000+
Focal Length Tolerance (%): ±5
Coating: Uncoated
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2
Clear Aperture CA (mm): 22.28
Edge Thickness ET (mm): 3.21
Center Thickness CT (mm): 12.27 ±0.30
f/#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 25.00
Radius R₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View