

TECHSPEC[®] 25mm Dia x 37.5mm FL, Uncoated, High Precision Aspheric Lens



TECHSPEC[®] High Precision Aspheric Lenses

Stock **#12-438** **20+ In Stock**

☐ [Other Coating Options](#)

-

1

+

A\$1,198⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$1,198.40 each
Qty 6-10	A\$1,078.40 each
Qty 11+	A\$1,006.40 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens

Type:

3D Surface Profile included with uncoated lenses

Note:

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.00/-0.025	
Centering (arcmin):	<1
Clear Aperture CA (mm):	22.50
Edge Thickness ET (mm):	5.49
Center Thickness CT (mm):	9.72
Bevel:	Protective as needed
Shape of Back Surface:	Plano
Optical Properties	
Effective Focal Length EFL (mm):	37.50 @ 587.6nm
Numerical Aperture NA:	0.33
Back Focal Length BFL (mm):	31.09
Substrate: ☐	N-BK7
Aspheric Design Wavelength (nm):	587.6
Asphere Figure Error, RMS @ 632.8nm:	λ/40
Coating:	Uncoated
Surface Quality:	40-20
f/#:	1.5
Wavelength Range (nm):	350 - 2200
Conjugate Distance:	Infinite
Power (diopters):	26.67
Regulatory Compliance	
RoHS 2015:	Compliant
Reach 219:	Compliant
Certificate of Conformance:	View

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Precision Aspheric Surface
- 3D Surface Profiles Included with Uncoated Lenses
- Uncoated and <0.25% Reflectance V-Coat Available

TECHSPEC® High Precision Aspheric Lenses guarantee better than λ/40 wave aspheric figure error. Achieved via precision magneto-rheological finishing (MRF), these aspheres offer high numerical apertures with diameters ranging from 15 to 50mm and are ideal for a variety of imaging and low light level applications. Each TECHSPEC High Precision Aspheric Lens is individually measured. 3D surface profiles are included with uncoated lenses. For diffraction-limited aspheres designed at specific Nd:YAG laser wavelengths, see our [TECHSPEC High Precision Laser Grade Aspheric Lenses](#).

Compatible Mounts

