

[See all 13 Products in Family](#)

TECHSPEC® 25mm Dia. x 3mm Thick, BBAR (2000-5000nm) Coated Barium Fluoride Window



Stock #23-529 **7 In Stock**

⊖ 1 ⊕ A\$550⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | A\$550.40 each |
| Qty 11-25 | A\$494.40 each |
| Qty 26-49 | A\$467.20 each |
| Need More? | Request Quote |

Product Downloads

General

Protective Window **Type:**
Crystal **Type of Window:**

Physical & Mechanical Properties

22.50 **Clear Aperture CA (mm):**

| | |
|----------------------|--|
| 25.00 +0.0/-0.1 | Diameter (mm): |
| 3.00 ±0.1 | Thickness (mm): |
| <3 | Parallelism (arcmin): |
| Protective as needed | Bevel: |
| 90.00 | Clear Aperture (%): |
| Fine Ground | Edges: |
| 0.34 | Poisson's Ratio: |
| 53 | Young's Modulus (GPa): |
| 82.00 | Knoop Hardness (kg/mm²): |

Optical Properties

| | |
|---|---|
| BBAR (2000-5000nm) | Coating: |
| Barium Fluoride (BaF ₂) | Substrate: □ |
| 1.48 | Index of Refraction (n_d): |
| 60-40 | Surface Quality: |
| 81.78 | Abbe Number (v_d): |
| Random | Axis Orientation: |
| R _{avg} <1.5% @ 2000-5000nm R _{abs} <3.0% @ 2000-5000nm R _{avg} <1.75% @ 2000-4000nm | Coating Specification: |
| 2000 - 5000 | Wavelength Range (nm): |
| λ/2 | Surface Flatness (P-V): |

Material Properties

| | |
|------|---|
| 4.89 | Density (g/cm³): |
| 18.1 | Coefficient of Thermal Expansion CTE (10⁻⁶/°C): |

Regulatory Compliance

| | |
|---------------------------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 235: |

Product Details

- Excellent Transmission from 200nm - 12µm
- Resistant to High-Energy Radiation
- Provide High Transmission without AR Coatings

TECHSPEC® Barium Fluoride (BaF₂) Windows can be used in a variety of applications, such as infrared spectroscopy, due to their wide broadband transmission that extends from the deep ultraviolet to the long-wave infrared. Barium fluoride's low index of refraction of 1.48 provides high transmission without the need for anti-reflection coatings. Barium fluoride windows can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the ultraviolet range. While barium fluoride windows are less resistant to water than calcium fluoride, BaF₂ windows are the most resistant optical fluoride to high-energy radiation, but feature lower UV transmittance. BaF₂ has a Knoop hardness of 82.

Note: These optical windows are very sensitive to thermal shock.

Barium fluoride is a fast scintillator and can be used to detect X-rays, gamma rays, or other high energy particles such as 511 keV gamma photons in Positron Emission Tomography (PET). BaF₂ can also be used to detect high-energy neutrons and separate them from simultaneously occurring gamma photons using pulse shape discrimination techniques.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts