

TECHSPEC® 25mm Dia x 50mm FL 8-12µm Coated, Ge Aspheric Lens



Stock **#68-257** 3-5 DAYS

[Other Coating Options](#)

- 1 + **A\$1,520.00**

ADD TO CART

Qty 1-5
A\$1,520.00
Qty 6+
A\$1,216.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
50.00 @4000nm

Numerical Aperture NA:
0.25

Back Focal Length BFL (mm):

48.44
Substrate: Germanium (Ge)
Aspheric Design Wavelength (nm): 4000
Asphere Figure Error, RMS @ 632.8nm: λ/6
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} <3.0% @ 8 - 12μm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 2.45
Center Thickness CT (mm): 3.00 ±0.10
f/#: 2.00
Bevel: Protective bevel as needed
Edges: Diamond Turned
Radius R₂ (mm): 142.9
Shape of Back Surface: Concave
Type: Aspheric Lens
Wavelength Range (nm): 8000 - 12000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant