

[See all 12 Products in Family](#)

**TECHSPEC® 25mm Dia. x 75mm EFL, Uncoated, Precision Laser Aspheric Lens**



Stock **#24-069** **17 In Stock**

⊖ 1 ⊕ A\$1,012.<sup>80</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | A\$1,012.80 each              |
| Qty 6-25       | A\$864.00 each                |
| Qty 26-49      | A\$763.20 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**Physical & Mechanical Properties**

|                       |                                  |
|-----------------------|----------------------------------|
| 25.00 +0.000 / -0.025 | <b>Diameter (mm):</b>            |
| 22.5                  | <b>Clear Aperture CA (mm):</b>   |
| 3.78                  | <b>Edge Thickness ET (mm):</b>   |
| 5.50 +0.000 / -0.10   | <b>Center Thickness CT (mm):</b> |

Protective as needed **Bevel:**

Plano **Shape of Back Surface:**

## Optical Properties

**Effective Focal Length EFL (mm):**  
75.00 @ 355nm

**Numerical Aperture NA:**  
0.16

**Back Focal Length BFL (mm):**  
70.9

**Substrate:**   
[Fused Silica](#)

**Asphere Figure Error, RMS @ 632.8nm:**  
λ/2 RMS and 2.5λ PV

**Coating:**  
Uncoated

**Surface Quality:**  
20-10

**f#:**  
1.5

**Design Wavelength DWL (nm):**  
355

**Wavelength Range (nm):**  
200 - 2200

**Conjugate Distance:**  
Infinite

**Slope Error Aspheric Side:**  
0.35μm/mm per 1mm Window

**Beam Deviation @ 587.6nm (arcmin):**  
<2.5

**Power (diopters):**  
13.33

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- Diffraction Limited at Designed Nd:YAG Laser Wavelengths
- Laser Damage Designed Coatings on UV Fused Silica Substrates
- Specified Slope Error to Guarantee Low Mid-Spatial Frequency Errors
- [High Precision Laser Grade Aspheric Lenses](#) are also Available

TECHSPEC® Precision Laser Aspheric Lenses are designed to maximize performance in high power laser applications. Featuring diffraction limited performance at their designed wavelengths these aspheric lenses are available with high laser damage threshold coatings optimized at the most common Nd:YAG laser wavelengths. With a λ/2 aspheric surface figure and 0.35μm/mm slope error, TECHSPEC® Precision Laser Aspheric Lenses minimize the mid-spatial frequency (MSF) errors and are ideal for integration into demanding laser processing, cutting, and additive manufacturing applications. Featuring UV fused silica substrates, these aspheres are highly durable and resistant to thermal expansion.