


[See all 26 Products in Family](#)

TECHSPEC[®]

25mm Diameter 45°, Red Dichroic Filter



Stock **#47-266** [CONTACT US](#)

-

1

+

A\$150^{.40}

ADD TO CART

Volume Pricing	
Qty 1+	A\$150.40 each
Need More?	Request Quote

Product Downloads

General

Dichroic Filter

Type:

Physical & Mechanical Properties

25.00

Diameter (mm):

4.00 ±0.20

Thickness (mm):

<1

Parallelism (arcmin):

Dimensional Tolerance (mm):

±0.25	
90.00	Clear Aperture (%):
Optical Properties	
45.00	Angle of Incidence (°):
615.00	Cut-On Wavelength (nm):
N-BK7	Substrate:
Traditional Coated	Coating:
Red	Color:
R _{abs} = 50% @ 615nm R _{avg} > 98% @ 640-750nm	Reflection (%):
640 - 750	Reflection Wavelength (nm):
60-40	Surface Quality:
90.00	Transmission (%):
400 - 595	Transmission Wavelength (nm):
±15	Wavelength Tolerance (nm):
Surface 1: Multi-Layer Dichroic Surface 2: Single Layer MgF ₂	Coating Specification:
400 - 750	Wavelength Range (nm):
λ/4	Surface Flatness (P-V):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Reflects Stated Color While Transmitting Remaining Visible Spectrum
- Ideal for Color Separation Applications
- Precision N-BK7 Substrates

TECHSPEC® 45° Reflective Dichroic Color Filters are designed to be used at a 45° angle of incidence and will reflect the stated color while transmitting the remaining visible wavelengths. EO's Reflective Dichroics boast higher performance and a better-quality substrate than other readily available color processing filters. Each filter provides greater than 98% reflection over the specified color range and greater than 90% transmission of the remaining wavelengths. TECHSPEC 45° Reflective Dichroic Color Filters are traditionally coated and feature an N-BK7 substrate. These filters are available in circular and square sizes.

Compatible Mounts