


TECHSPEC® 25mm Diameter MgF₂ Coated, Ultra-Thin N-BK7 Window

See More by [SCHOTT Optical Components](#)



Ultra-Thin N-BK7 Windows

Stock **#66-196** 3-5 DAYS

- 1 + **A\$188.00**

ADD TO CART

Qty 1-5
A\$188.00
Qty 6+
A\$150.40
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
64.17

Bevel:
Protective as needed

Clear Aperture CA (mm):
22.50

Diameter (mm): 25.00 +0.00/-0.10
Thickness (mm): 0.20 ±0.025
Coating: MgF₂ (400-700nm)
Coating Specification: R_{avg} ≤1.75% @ 400 - 700nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcsec): <30
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Quality: 20-10
Transmitted Wavefront, P-V: λ/2
Type: Protective Window
Wavelength Range (nm): 400 - 700
Young's Modulus (GPa): 82
Damage Threshold, Reference:  10 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View