

TECHSPEC® 25mm Diameter x 100mm FL, 355nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCXLenses

Stock **#67-956 5 In Stock**  

☐ Other Coating Options

-

1

+

A\$369<sup>60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | A\$369.60 each                |
| Qty 6-25       | A\$296.00 each                |
| Qty 26-49      | A\$270.40 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.00/-0.10

Centering (arcmin):

|                                 |                                  |
|---------------------------------|----------------------------------|
| <1                              |                                  |
| 3.79 ±0.10                      | Center Thickness CT (mm):        |
| 2.05                            | Edge Thickness ET (mm):          |
| 22.5                            | Clear Aperture CA (mm):          |
| Protective as needed            | Bevel:                           |
| Optical Properties              |                                  |
| 100.00 @ 587.6nm                | Effective Focal Length EFL (mm): |
| 97.40                           | Back Focal Length BFL (mm):      |
| Laser V-Coat (355nm)            | Coating:                         |
| R <sub>abs</sub> <0.25% @ 355nm | Coating Specification:           |
| Fused Silica (Corning 7980)     | Substrate: □                     |
| 20-10                           | Surface Quality:                 |
| λ                               | Power (P-V) @ 632.8nm:           |
| λ/10                            | Irregularity (P-V) @ 632.8nm:    |
| ±1                              | Focal Length Tolerance (%):      |
| 45.85                           | Radius R <sub>1</sub> (mm):      |
| 4.00                            | f/#:                             |
| 0.13                            | Numerical Aperture NA:           |
| 355                             | Design Wavelength DWL (nm):      |
| 7.5 J/cm² @ 355nm, 20ns, 20Hz   | Damage Threshold, By Design: □   |
| Regulatory Compliance           |                                  |
| Compliant                       | RoHS 2015:                       |
| Compliant                       | REACH 201:                       |
| View                            | Certificate of Conformance:      |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Guaranteed Laser Damage Threshold
- 10-5 Surface Quality
- λ/10 Surface Accuracy

TECHSPEC® Laser Grade PCX Lenses are designed for high energy Nd:YAG laser applications including laser cutting, machining, and welding. The precision fused silica substrate, featuring λ/10 surface accuracy and 10-5 surface quality, ensures low scatter and excellent transmitted wavefront performance. TECHSPEC® Laser Grade PCX Lenses are available uncoated or with a variety of high laser damage threshold anti-reflection (AR) coating options. Coatings are available at the most common Nd:YAG laser wavelengths to ensure maximum laser throughput.



LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information



Compatible Mounts