

[See all 35 Products in Family](#)

TECHSPEC® 25mm Diameter x 17.5mm FL, VIS Coated, K22R Plastic Aspheric Lens



TECHSPEC® Plastic Aspheric Lenses

Stock **#21-210** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **A\$116⁰⁰**

ADD TO CART

Volume Pricing

Qty 1-24	A\$116.80 each
Qty 25-99	A\$83.20 each
Qty 100-249	A\$60.80 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

25.00 ±0.15 **Diameter (mm):**

Centering (arcmin):

<5 (by design)

21.5 Clear Aperture CA (mm):

1.05 Edge Thickness ET (mm):

10.90 ± 0.20 Center Thickness CT (mm):

Protective as needed Bevel:

Convex Shape of Back Surface:

Optical Properties

17.50 @ 587.6nm Effective Focal Length EFL (mm):

0.71 Numerical Aperture NA:

11.22 Back Focal Length BFL (mm):

Zeonex K22R Substrate:

587.6 Aspheric Design Wavelength (nm):

BBAR (425-675nm) Coating:

$R_{avg} < 0.7\%$ @ 425 - 675nm Coating Specification:

80-50 Surface Quality:

0.7 f#:

50.47 Radius R_2 (mm):

425 - 675 Wavelength Range (nm):

Infinite Conjugate Distance:

587.60 Focal Length Specification Wavelength (nm):

Environmental & Durability Factors

-30 to 70 Operating Temperature (°C):

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 250:

Product Details

- Full Prescription Data Available
- Standard 25mm Diameter for Easy System Integration
- High Numerical Aperture Designs for Superior Light Collection

TECHSPEC® Plastic Aspheric Lenses offer a lightweight alternative to glass spherical or aspherical lenses. Designed with a standard 25mm diameter, these lenses can be easily integrated into most systems and applications using standard mounting hardware. The plastic substrate provides exceptional value while still maintaining excellent performance and a high numerical aperture. TECHSPEC® Plastic Aspheric Lenses feature low haze, low autofluorescence, and excellent coating adhesion, making these lenses ideal for OEM and research applications alike. For alternate designs or custom coating requirements, please contact our [Sales Department](#).

Technical Information



