

## 25mm FL, T-Mount Focusing Assembly



Stock **#53-044** **1 In Stock**

A\$195<sup>.20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	A\$195.20 each
Qty 10-24	A\$175.68 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

Accessory

Type of Illumination:

### Physical & Mechanical Properties

55.00 Total Length (mm):

48.00 Outer Diameter (mm):

## Optical Properties

15.4 **Beam Divergence (°):**

25.00 **Focal Length FL (mm):**

1.6 **Spot Size at 6" Working Distance (inches):**

## Threading & Mounting

T-mount **Mount:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Reduce Divergence of Fiber Optic Light Guides
- Available in C- or T-Mount or Slim Mount
- Shape Output over Small Areas

Fiber-Lite Focusing Lenses are an essential component in reducing divergence of fiber optic light guides. Fiber optic light guides project a large, diffuse beam of light – not a collimated or focused spot. Lens assemblies at the end of the fiber can collect light efficiently and shape the output effectively over smaller areas. Fiber-Lite Focusing Lenses are available in two configurations – mounted in our C- and T-Mount components, or in a slim mount for direct integration with many of our light guides. The C- and T-Mount configuration requires a standard [Dolan-Jenner adapter](#), and can be used with any light guide. Additional accessories may be added with our [C- and T-Mount components](#). Stock [#58-837](#) can be used with any of our 1/8" or 1/4" light guides with tip diameters of 0.187" or 0.312". [#58-836](#) can be used with our semi-rigid and hybrid light guides with end-tip diameter of 0.500".