

TECHSPEC® 266nm 1X - 3X Research-Grade Variable Beam Expander



Research-Grade Variable Beam Expanders



Stock **#87-559** 3-5 DAYS

- 1 +

A\$2,280.00

ADD TO CART

Qty 1-4
A\$2,280.00
Qty 5+
A\$2,008.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0 ±0.06

Coating:
Laser V-Coat (266nm, 355nm)

Design Wavelength DWL (nm): 266
Entrance Aperture (mm): 10
Exit Aperture (mm): 30
Expansion Power: 1X - 3X
Substrate: Fused Silica (Corning 7980)
Length (mm): 172.30
Mounting Threads: Input: Male C-Thread (1" x 32 TPI) Output: Male T-Thread (M42 x 0.75)
Transmission (%): >95 @ DWL
Type: Beam Expander
Weight (g): 577
Housing Diameter (mm): 58.2
Transmitted Wavefront, P-V: <λ/4 @ 266nm for Input Beam ≤5mm
Coating Specification: R_{abs} <0.25% @ 265 - 267nm R_{abs} <0.25% @ 354 - 356nm R_{avg} <1.0% @ 260 - 365nm
Wavelength Range (nm): 260 - 365
Style: Variable Magnification
Damage Threshold, By Design: 2 J/cm² @ 10ns, 20 Hz, 266nm
Divergence Adjustment: Non-Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View