

## 28.5 x 41mm FL, Grade 1, Double-Convex Lens



Stock **#75-035** CLEARANCE **5 In Stock**

-

1

+

A\$16<sup>.40</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | A\$16.40 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| Physical & Mechanical Properties |                                  |
|----------------------------------|----------------------------------|
| 28.50                            | Diameter (mm):                   |
| Optical Properties               |                                  |
| 41.00                            | Effective Focal Length EFL (mm): |
| 0.35                             | Numerical Aperture NA:           |
| Regulatory Compliance            |                                  |

## Product Details

- Ideal for Experimenting and Prototyping Applications
  - Quantities Extremely Limited, Buy While Supplies Last
  - For Even Mbre Deals, Check out [Mega Clearance: Optics](#)
- Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

20 - 29.9mm Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## Technical Information

