

TECHSPEC® 2" Dia, 8" FL UV Enhanced Alum., Spherical Mirror



Stock #49-608

CONTACT US

-

1

+

A\$272.00

ADD TO CART

Qty 1-9

A\$272.00

Qty 10+

A\$231.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Substrate:

BOROFLOAT®

Focal Length Tolerance (%):

±2

Surface Quality:

60-40

Surface Accuracy:

N4
Diameter (inches): 2.0
Diameter (mm): 50.80 +0.5/-0
Diameter Tolerance (inches): +0.02/-0
Effective Focal Length EFL (inches): 8.00
Effective Focal Length EFL (mm): 203.20
Radius of Curvature (mm): 406.40
Aperture (f/#): f/4
Coating: Enhanced Aluminum (250-700nm)
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: 0.5 J/cm ² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant