

TECHSPEC® 2X, 0.15 NA, UCf Objective



Stock **#36-278** [CONTACT US](#)

A\$387²⁰

ADD TO CART

Volume Pricing	
Qty 1-2	A\$387.20 each
Qty 3-4	A\$356.80 each
Qty 5-9	A\$348.80 each
Need More?	Request Quote

Product Downloads

General

Fluorite **Type:**

Finite Conjugate **Style:**

Edmund Optics® **Manufacturer:**

Physical & Mechanical Properties

10.80 Length (mm):

29.0 Maximum Diameter (mm):

19 Weight (g):

Optical Properties

4.4 Horizontal Field of View, 1/2" Sensor:

7.04 Horizontal Field of View, 1.1" Sensor:

8.00 Focal Length FL (mm):

2X Magnification:

0.15 Numerical Aperture NA:

4.44 Resolving Power (μm):

12.00 Depth of Field (μm):

11.3 Working Distance (mm):

400 - 700 Wavelength Range (nm):

17.6 Field Number (mm):

Sensor

1.1" Maximum Sensor Format:

Threading & Mounting

C-Mount Mount:

C-Mount Mounting Threads:

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Compact Finite Conjugate Objectives
- Mount Directly to a C-Mount Camera
- Near Diffraction Limited performance

TECHSPEC® UCf Objective Series are compact objectives that are finite conjugate by design, but achieve similar imaging performance of infinity corrected objectives and do not require a secondary tube lens to generate an image on the sensor. Available at 2X, 4X, 5X, 10X, 15X, and 20X magnifications. These objectives mount directly to a C-mount camera without additional extension tubes.