

[See all 5 Products in Family](#)

28mm FL, Focusing Assembly for Hybrid/Semi-Rigid



Stock #58-836 **3 In Stock**

A\$124.⁸⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$124.80 each
Qty 10-24	A\$112.32 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Accessory

Type of Illumination:

Physical & Mechanical Properties

60.325

Total Length (mm):

22.352

Outer Diameter (mm):

Optical Properties

8.3 **Beam Divergence (°):**

28.00 **Focal Length FL (mm):**

0.87 **Spot Size at 6" Working Distance (inches):**

Threading & Mounting

N/A **Mount:**

Regulatory Compliance

[Compliant](#) **Reach 174:**

[View](#) **Certificate of Conformance:**

Product Details

- Reduce Divergence of Fiber Optic Light Guides
- Available in C- or T-Mount or Slim Mount
- Shape Output over Small Areas

Fiber-Lite Focusing Lenses are an essential component in reducing divergence of fiber optic light guides. Fiber optic light guides project a large, diffuse beam of light – not a collimated or focused spot. Lens assemblies at the end of the fiber can collect light efficiently and shape the output effectively over smaller areas. Fiber-Lite Focusing Lenses are available in two configurations – mounted in our C- and T-Mount components, or in a slim mount for direct integration with many of our light guides. The C- and T-Mount configuration requires a standard [Dolan-Jenner adapter](#), and can be used with any light guide. Additional accessories may be added with our [C- and T-Mount components](#). Stock [#58-837](#) can be used with any of our 1/8" or 1/4" light guides with tip diameters of 0.187" or 0.312". [#58-836](#) can be used with our semi-rigid and hybrid light guides with end-tip diameter of 0.500".