

[See all 12 Products in Family](#)

2.8mW, 650nm, A Gated Cameo Laser



Stock **#72-689** **1 In Stock**

- 1 + **A\$187²⁰**

ADD TO CART

Volume Pricing	
Qty 1-9	A\$187.20 each
Qty 10+	A\$177.84 each
Need More?	Request Quote

Product Downloads

General

Mean Time To Failures MTTF @ 25° (hours):
≥50,000

Compatible with Interchangeable Optics:
[#73-168](#)
[#73-169](#)
[#73-172](#)
[#73-175](#)

Note:

#73-179	
Diode	Type of Laser:
IIIR	Laser Class - CDRH:
Physical & Mechanical Properties	
14 x 14	Dimensions (mm):
15	Weight (g):
24	Housing Length (mm):
Optical Properties	
650.00	Wavelength (nm):
3.1	Beam Diameter (mm):
<0.4	Beam Divergence (mrad):
Red	Color:
25mm - ∞	Focus Range (mm):
Electrical	
2.8	Output Power (mW):
±1.5	Power Stability (%):
Hardware & Interface Connectivity	
Free Space	Output Type:
JST 4 Pin	Connector:
4.5	Input Voltage (V):
Environmental & Durability Factors	
-10 to +45	Operating Temperature (°C):
-40 to +85	Storage Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- TTL Modulation up to 100kHz
- Compact 24 x 14 x 14mm Housing with M12 x 1 Threaded Barrel
- 635, 650, and 670nm Wavelength Options

Compact Gated Industrial Laser Diode Modules provide a high quality, cost effective OEM solution for a range of industrial applications. Featuring a gated CW laser output, these modules can achieve switching speeds up to 100kHz through the control input or they can be operated from low power TTL and microprocessors to achieve a simple, slow speed ON/OFF switching. An electrically isolated compact 24 x 14 x 14mm housing and M12 x 1 threaded barrel facilitates efficient cooling through good thermal contact and allows for easy integration into existing OEM laser systems. Compact Gated Industrial Laser Diode Modules are ideal for a wide range of industrial OEM applications including machine vision, inspection, positioning, and alignment. When operated within the appropriate temperature range (-10 to 55°C), these lasers can achieve long lifetimes with minimum mean time between failures (MTTF) ranging from ≥30,000 to ≥120,000 hours depending on wavelength.

Note: Interchangeable optics only compatible with A series Gated Cameo Lasers #72-688 and #72-689. C2 series lasers, #72-684 and #72-686, feature a fixed 2mm aperture lens, and S series lasers, #72-685 and #72-687, feature a fixed standard collimating lens that produces a beam size of 5 x 1.5mm.