

TECHSPEC® 2° Nom. Uncoated, N-BK7 Wedge Prism



Stock **#43-651** 3-5 DAYS

- 1 +

A\$76.00

ADD TO CART

Qty 1-5
A\$76.00
Qty 6+
A\$60.80
Volume Pricing
Request Quote

Get Product Downloads



Coating:
Uncoated

Angle Tolerance (arcsec):
±30

Bevel:
Protective bevel as needed

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

7.1
Design Wavelength DWL (nm): 632.8
Diameter (mm): 25.00 +0.00/-0.10
Image Orientation: Beam Deviation
Power (diopters): 3.49
Ray Deviation @ 633nm (°): 2.00
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 3.00
Type: Wedge Prism
Wavelength Range (nm): 350 - 2200
Wedge Angle: 3° 52'
Maximum Edge Thickness (mm): 4.7

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View