

[See all 40 Products in Family](#)

3" Length, 8-32 and 1/4-20, Steel Post



Stock #72-785 NEW 12 In Stock

-

1

+

A\$10⁻⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$10.40 each
Need More?	Request Quote

Product Downloads

General

English	Type:
---------	-------

Physical & Mechanical Properties

12.7	Diameter (mm):
0.5	Diameter (inches):
76.2	Length (mm):
	Length (inches):

Threading & Mounting

Thread 1: 8-32
Thread 2: 1/4 - 20

Male Thread:

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 250:

Product Details

- English or Metric Versions Options Available
 - Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
 - Removable Top and Bottom Set Screws Available
- Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x 0.7/M6 x 1.0 for Metric; 8-32/¼-20 for English) are laser-engraved on the ends of each post for quick identification and integration.
- Note:** All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.