

TECHSPEC®

2X, 0.13 NA, UCf Objective



Stock **#36-280** 3-5 DAYS

-

1

+

A\$416.00

ADD TO CART

Qty 1-2

A\$416.00

Qty 3+

A\$385.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
4.4

Horizontal Field of View, 1.1" Sensor:
7.04

Focal Length FL (mm):
10.00

Length (mm):
21.20

Magnification: 2X
Maximum Diameter (mm): 29.0
Maximum Sensor Format: 1.1"
Mount: C-Mount
Numerical Aperture NA: 0.13
Mounting Threads: C-Mount
Type: Fluorite
Resolving Power (μm): 5.12
Depth of Field (μm): 16.02
Working Distance (mm): 9.9
Weight (g): 27
Wavelength Range (nm): 400 - 700
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Field Number (mm): 17.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View