


30° Fan Angle, 400 - 500nm AR Coated, High Precision Powell Lens



Stock #70-132 **1 In Stock**

⊖ 1 ⊕ A\$520⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$520.00 each
Qty 11-49	A\$467.20 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Beam Shaping Lens **Type:**

Physical & Mechanical Properties

Dimensions (mm):

8.90 +0.00/-0.15

Height (mm):

8.90 +0.00/-2.00

Input Beam Diameter, $1/e^2$ (mm):

1.3

Optical Properties

[N-BK7](#)

Substrate:

BBAR (400-500nm)

Coating:

400 - 500

Wavelength Range (nm):

$R_{\text{abs}} < 1.0\%$ @ 400 - 500nm

Coating Specification:

1.458

Index of Refraction (n_d):

30.00

Fan Angle (°):

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- Generate Uniform, Flat-Top Profile Over Entire Line
- Fan Angles from 1° to 75° Available
- AR Coated for 400 - 500nm or 500 - 850nm

Precision Powell Lenses, also known as aspheric line generators (ALGs), spread an input beam across a uniform line with a top-hat beam profile at a specified fan angle. These Powell lenses are produced through a precision manufacturing process to ensure high contained power, uniformity, and line straightness across the entire produced line, as well as superior part-to-part consistency. They are designed for a specific input beam diameter to provide best line uniformity; larger input beams will result in higher intensity at the ends of the generated line, while smaller will create a more Gaussian distribution. Precision Powell Lenses are ideal for use in machine vision and life science applications including 3D profile measurement, PCB inspection, line-scan SD-OCT, line-scan confocal microscopy, flow cytometry, and particle analysis.