


[See all 60 Products in Family](#)

TECHSPEC[®]

3" Dia, 12" FL 750-1100nm, Spherical Mirror



Stock **#73-027** 3 In Stock

-

1

+

A\$686⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$686.40 each
Qty 6-24	A\$547.20 each
Need More?	Request Quote

Product Downloads

General

Spherical Mirror

Type:

Physical & Mechanical Properties

76.20 +1.0/-0

Diameter (mm):

Ground

Back Surface:

3.0	Diameter (inches):
+0.04/-0	Diameter Tolerance (inches):

0.50	Edge Thickness ET (inches):
12.70	Edge Thickness ET (mm):

+0.0/-15	Edge Thickness Tolerance (%):
----------	-------------------------------

Optical Properties

Dielectric	Coating Type:
Dielectric Mirror (750-1100nm)	Coating:

750 - 1100	Wavelength Range (nm):
304.80	Effective Focal Length EFL (mm):

BOROFLOAT®	Substrate: □
f/4	Aperture (f/#):

R _{avg} >98% @ 750 - 1100nm (0 - 45°) R _{avg} >99% @ 750 - 1100nm (0°)	Coating Specification:
12.00	Effective Focal Length EFL (inches):

±2	Focal Length Tolerance (%):
λ/4	Surface Accuracy:

60-40	Surface Quality:
1 J/cm² @ 1064nm, 20ns, 20Hz	Damage Threshold, By Design: □

609.60	Radius of Curvature (mm):
--------	---------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Ideal for Multispectral Focusing Applications
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Multiple Sizes Available

TECHSPEC® Broadband Dielectric Spherical Mirrors are ideal for light collection in multispectral imaging applications. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. ABOROFLOAT® substrate provides a good combination of performance and value. TECHSPEC® Broadband Dielectric Spherical Mirrors are available in diameters ranging from 25.4 to 152.4mm for ease of system integration. These mirrors collect and focus light without introducing chromatic aberration.

Technical Information

