

30 x 30mm Broadband Hybrid Diffuser



Broadband Hybrid Diffusers

Stock **#70-255** 20+ In Stock

-

1

+

A\$79²⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$79.20 each
Qty 11-49	A\$63.20 each
Need More?	Request Quote

Product Downloads

General

Type:

Opal Diffuser

Physical & Mechanical Properties

Dimensions (mm):

30.00 x30.00 ±0.25

Grit:

120

Thickness (mm):

1.75 ±0.10	
30.00	Width (mm):
30.00	Length (mm):
Optical Properties	
Uncoated	Coating:
White Diffusing Glass	Substrate:
400 - 1100	Wavelength Range (nm):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Surface Treated Semi-Opaque White Glass
- Two Mechanisms of Scatter
- Excellent Scattering into the NIR

Broadband Hybrid Diffusers are semi-opaque diffusers designed to scatter efficiently from the UV to the NIR. Featuring surfaces sandblasted with 120-grit and a 1.75mm thick scattering medium, these diffusers uniquely offer two mechanisms of scatter. Each scatter mechanism has its own wavelength dependency, and when combined on a single optic, produce a diffuser that scatters across a wide spectral region. Broadband Hybrid Diffusers are ideal for applications that require high scatter for even illumination and can be used as view screens.