

300µm Aperture Diameter, Chrome on Glass Aperture



Stock #90-740 **NEW** 1 In Stock

1

A\$296^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$296.00 each
Need More?	Request Quote

Physical & Mechanical Properties

Outer Diameter (mm): 25.4	Fixed Aperture Diameter (µm): 300 ± 5.0
Thickness (inches): 0.06 ±0.004	Thickness (mm): 1.52
Thickness Tolerance (mm): ±0.1	

Optical Properties

Coating: Low Reflective Chrome	
---------------------------------------	--

Regulatory Compliance

Certificate of Conformance: View	
---	--

Product Details

- Chrome Coating on Glass Substrate
- Ideal for Precise Beam Control, Modulation, or Optical Alignment
- Pinhole Diameters Ranging from 10µm to 1,000µm

Chrome Coated Glass Optical Apertures are composed of soda lime float glass with low reflective chrome coating for high-contrast performance. These apertures are designed with pinhole diameters ranging from 10µm to 1000µm. The apertures have an overall diameter of 25.4mm (1") and a thickness of 1.52mm, ensuring easy integration with a wide variety of optical mounts. Chrome coating on glass provides a stable and circular aperture diameter immune to bending or creasing. Chrome Coated Glass Optical Apertures are designed to provide high-precision light control, ideal for beam shaping, spatial filtering, and alignment in advanced photonic systems.