

TECHSPEC® 30.0mm 400 - 750nm Coated, N-BK7 Right Angle Mirror



Broadband Dielectric Coated Right Angle Mirrors

Stock **#87-392** [CONTACT US](#)



1



A\$400.00

ADD TO CART

Qty 1-5

A\$400.00

Qty 6+

A\$320.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:
Dielectric Mirror (400-750nm)

Coating Specification:
Hypotenuse: R_{avg} >98% @ 400 - 750nm (0 - 45°)
R_{avg} >99% @ 400 - 750nm (0°)

Wavelength Range (nm):
400 - 750

Length of Legs (mm): 30.00
Length of Hypotenuse (mm): 42.40
Surface Flatness (P-V): λ/4
Substrate: N-BK7
Surface Quality: 40-20
Dimensional Tolerance (mm): ±0.1
Coating Type: Dielectric
Angle Tolerance (arcmin): ±2
Clear Aperture (%): 90
Type: Right Angle Mirror
Damage Threshold, By Design: 0.5 J/cm2 @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View