

TECHSPEC®

30.0mm Dia. x 120.0mm FL, VIS-EXT, Inked, Plano-Convex Lens



Stock **#88-752-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

A\$100.80

ADD TO CART

Qty 1-9
A\$100.80
Qty 10+
A\$90.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):
120.00 @587.6nm

Back Focal Length BFL (mm): 116.04
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 6.00 ±0.10
Edge Thickness ET (mm): 4.16
Radius R₁ (mm): 62.02
Clear Aperture CA (mm): 29
f/#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View