

[See all 12 Products in Family](#)

## 300µm Aperture Diameter, Chrome on Glass Aperture



Stock #90-740 **NEW** 2 In Stock

- 1 + A\$296<sup>.00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	A\$296.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

25.4 Outer Diameter (mm):

300 ± 5.0 Fixed Aperture Diameter (µm):

0.06 ± 0.004 Thickness (inches):

1.52 Thickness (mm):

±0.1 Thickness Tolerance (mm):

## Optical Properties

Low Reflective Chrome

Coating:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Chrome Coating on Glass Substrate
- Ideal for Precise Beam Control, Modulation, or Optical Alignment
- Pinhole Diameters Ranging from 10 $\mu$ m to 1,000 $\mu$ m

Chrome Coated Glass Optical Apertures are composed of soda lime float glass with low reflective chrome coating for high-contrast performance. These apertures are designed with pinhole diameters ranging from 10 $\mu$ m to 1000 $\mu$ m. The apertures have an overall diameter of 25.4mm (1") and a thickness of 1.52mm, ensuring easy integration with a wide variety of optical mounts. Chrome coating on glass provides a stable and circular aperture diameter immune to bending or creasing. Chrome Coated Glass Optical Apertures are designed to provide high-precision light control, ideal for beam shaping, spatial filtering, and alignment in advanced photonic systems.