

TECHSPEC®

30mm Dia., 0.86 Numerical Aperture, 350-700nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-965-INK** 10-15 DAYS

[Other Coating Options](#)



1



A\$848.00

ADD TO CART

Qty 1-5

A\$848.00

Qty 6+

A\$678.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):
17.50 @ 587.6nm

Numerical Aperture NA: 0.86
Back Focal Length BFL (mm): 10.30
Substrate: N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: VIS-EXT+ (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm @ ±30° AOI R _{abs} <1.5% @ 350 - 700nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 27.00
Edge Thickness ET (mm): 4.17
Center Thickness CT (mm): 13.00 ±0.10
f#: 0.58
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View