

TECHSPEC[®] 30mm Dia., 0.86 Numerical Aperture, Uncoated, Precision Aspheric Lens



TECHSPEC[®] Precision Aspheric Lenses

Stock **#37-432** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$720.00

ADD TO CART

Qty 1-5

A\$720.00

Qty 6+

A\$576.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
30.00 +0.00/-0.025

Effective Focal Length EFL (mm):
17.50 @ 587.6nm

Numerical Aperture NA:
0.86

Back Focal Length BFL (mm): 10.30
Substrate: N-SF6
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 27.00
Edge Thickness ET (mm): 4.17
Center Thickness CT (mm): 13.00 ±0.10
f/#: 0.58
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 390 - 2500
Conjugate Distance: Infinite
Power (diopters): 57.14

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant