

[See all 18 Products in Family](#)

TECHSPEC®

30mm, 40mm Radius, English Goniometer



30mm, 40mm Radius, English Goniometer

Stock **#66-520** **2 In Stock**

-

1

+

A\$656⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-2	A\$656.00 each
Qty 3+	A\$572.32 each
Need More?	Request Quote

Product Downloads

General

English	Type:
5	Resolution (arcmin):

Physical & Mechanical Properties

Goniometer	Type of Movement:
	Stage Size (mm):

30 x 30

Travel (°):

± 15

Construction:

Brass Stage

Leadscrew Pitch (mm):

0.5

Load Capacity (kg):

2

Radius R (mm):

40

Stage Size (inches):

1.18 x 1.18

Weight (kg):

0.15

Hardware & Interface Connectivity

Type of Drive:

Lead Screw

Threading & Mounting

Mounting Threads:

(1) $\frac{1}{4}$ -20, (8) 2-56

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

View

REACH 241:

Compliant

Product Details


Bottom adapter plates, sold separately, are required to mount 30mm and 40mm stages to standard breadboards.

- Metric and English Hole Patterns Available
- Stackable for Two-Axis Rotation
- Mechanically Compatible with our **TECHSPEC® Stages**




TECHSPEC® Goniometers allow for precise angular adjustment of an object about a fixed point located above the center of the mounting surface. They provide true tip and tilt adjustment of any optical component and are often used to accurately direct lasers and align mirrors in beam steering applications. These goniometers are available in with Metric and English hole patterns. TECHSPEC® Goniometers are available in different plate sizes to accommodate a host of applications. Each size is offered in several radii of movement for easily stacking into two axis configurations. To provide motion about a common point in two different axes, mount goniometer stages with smaller radii on top of those with larger radii of the same stage size.

Each goniometer stage features precision movement along a dovetail design with a vernier scale for high-resolution measurements and movement repeatability. A locking thumbscrew allows each to be held securely in place. 30mm and 40mm goniometer stages are constructed of durable black painted brass, while 70mm goniometer stages are constructed of black anodized aluminum. [Bottom adapter plates](#), sold separately, are required to mount 30mm and 40mm stages to standard breadboards; 70mm stages will mount directly.

Technical Information



30mm Goniometers



Item No.	English Name	Material	Dimensions (mm)	Weight (g)	Notes
40	30mm Goniometer	Aluminum	30 x 30 x 28.5	7.4	
41	30mm Goniometer	Aluminum	30 x 30 x 28.5	7.4	
42	30mm Goniometer	Aluminum	30 x 30 x 28.5	7.4	