

30mm Dia. 632.8nm $\lambda/4$ Quartz Waveplate Zero Order



Stock **#48-491** [CONTACT US](#)

- 1 + **A\$1,024.00**

ADD TO CART

Qty 1-5
A\$1,024.00
Qty 6+
A\$832.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
23.0

Coating:
Laser V-Coat (632.8nm)

Design Wavelength DWL (nm):
632.8

Diameter (mm):
30.00 +0.00/-0.25

Substrate: Crystal Quartz
Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 6.00 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/8 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0001
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View