

TECHSPEC[®] 30mm Dia., 1mm Thick, MgF₂ Coated, B270 Window

See More by [SCHOTT Optical Components](#)



Stock #17-176 3-5 DAYS



1



A\$73.60

ADD TO CART

Qty 1-5

A\$73.60

Qty 6+

A\$59.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Abbe Number (v_d):
58.3

Bevel:
Protective as needed

Clear Aperture CA (mm):
27.00

Diameter (mm): 30.00 +0.00/-0.25
Thickness (mm): 1.00 ±0.10
Coating: MgF ₂ (632.8nm)
Coating Specification: R _{avg} ≤1.50% @ 632.8nm (N-BK7)
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 9.4 (+20 to +300°C)
Density (g/cm³): 2.56
Edges: Fine Ground
Index of Refraction n_d: 1.523
Knoop Hardness (kg/mm²): 500
Poisson's Ratio: 0.22
Substrate: B270
Surface Flatness (P-V): 1λ (per 25.4mm Dia. within CA)
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 400 - 700
Young's Modulus (GPa): 71.5
Damage Threshold, By Design: ☐ 10 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant