

TECHSPEC[®] 30mm Dia. x 100mm FL, YAG-BBAR Coated, Inked, Double-Convex Lens



YAG-BBAR Coated Double-Convex (DCX) Lenses



Stock **#89-280-INK** 10-15 DAYS

-

1

+

A\$108.80

ADD TO CART

Qty 1-9

A\$108.80

Qty 10+

A\$98.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Back Focal Length BFL (mm):
98.34

Effective Focal Length EFL (mm): 100.00
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate:  N-BK7
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.79
Radius R₁=R₂ (mm): 102.5
Clear Aperture CA (mm): 29.00
f/#: 3.33
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.15
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View